



Fabric Sample Cutter


Model: FT-100CM2

Getting started


1. Screw in the handle



2. Screw in three rubber pads on the bottom



3. Lay the **PVC board** in the middle of the bottom metal plate before use. Place the fabric or paper on the PVC board then pull down the handle to cut samples



WARNINGS:

The equipment is to be used by one person at a time to avoid injury. Children must not use this equipment. The cutting blade and bottom plate has been adjusted at its optimal condition. **Operator should not attempt to adjust the cutting blade** (see below) or it will affect the cutting results.



HCL Asia Ltd.

Unit 14, 6/F., Worldwide Industrial Centre,
43-47 Shan Mei Street, Fotan, Shatin, Hong Kong
T: +852 27420018 F: +852 27420053
info@hcl-asia.com.hk

www.hcl-asia.com.hk

Specifications:

Cutting area: 100cm²
Cutting thickness: 0.1mm-10mm
Machine size: 335 * 235 * 540mm
Blade size: diameter 112.84mm (circle area=100 cm²)
Outer packing size: 400 * 260 * 370mm
2x cutting pads included
Total weight: 14KG